


No: 20132-113

APC applicator 300 A



Dimensions and weight

Dimensions	Ø 2,3 mm
Length	300 mm

Basic features

Flexibility	rigid
Beam forms	A = Axial Beam
Shape / Forming	A

Cleaning and Reprocessing

Cleaning in washer disinfectant	max 95 °C
Sterilization in autoclave	max 138 °C

Standards

Classification acc. to 93/42 EWG	IIb
Protection category acc. to EN 60 601-1	
Type acc. to EN 60 601-1	

Additional product information

Packaging unit	1 Piece
Max. electrical capacity	4.3 kVp