

No: 20190-093

Slim-Line electrosurgical pencil with rocker switch



Dimensions and weight

Cable length	with connecting cable 4 m
Shaft diameter	4 mm

Basic features

Compatibility	VIO, ICC, ACC, non-ERBE units
Connection	International

Cleaning and Reprocessing

Cleaning in washer disinfectant	max 95 °C
Sterilization in autoclave	max 138 °C

Standards

Classification acc. to 93/42 EWG	IIb
Protection category acc. to EN 60 601-1	
Type acc. to EN 60 601-1	

Additional product information

Packaging unit	1 Piece
Max. electrical capacity	2.5 kVp