

No: 20191-239



Shaft extension

Dimensions and weight

| | |
|----------------|--------|
| Dimensions | ø 4 mm |
| Shaft diameter | 4 mm |
| Length | 180 mm |

Surface

| | |
|------------|-----------------|
| Insulation | shaft insulated |
|------------|-----------------|

Cleaning and Reprocessing

| | |
|---------------------------------|------------|
| Cleaning in washer disinfectant | max 95 °C |
| Sterilization in autoclave | max 134 °C |

Standards

| | |
|---|-----|
| Classification acc. to 93/42 EWG | Ila |
| Protection category acc. to EN 60 601-1 | |
| Type acc. to EN 60 601-1 | |

Additional product information

| | |
|--------------------------|---------|
| Max. electrical capacity | 4 kVp |
| Packaging unit | 1 Piece |