

No: 20191-157

Hook electrode, round



Dimensions and weight

Dimensions	Ø 5 mm
Length	320 mm

Surface

Insulation	shaft insulated
Coating	with non-adhesive coating

Cleaning and Reprocessing

Cleaning in washer disinfectant	max 95 °C
Sterilization in autoclave	max 134 °C

Standards

Classification acc. to 93/42 EWG	IIb
Protection category acc. to EN 60 601-1	
Type acc. to EN 60 601-1	

Additional product information

Max. electrical capacity	4.3 kVp
Packaging unit	1 Piece